












- 15 HPC CONNECTIONS SHOWN ARE FOR
410A REFRIGERANT. FOR R22 REFRIGERANT
(DIGIT 7 IN MODEL NUMBER LEADS "A" OR "B")
HPC01 WILL HAVE BLACK LEADS AND
HPC02 WILL HAVE RED LEADS



THERMOSTAT



4366-1531

REV
11

M

DIAGRAM

CONNECTION PRINT - GAS HEAT.

7.5-10 TON, 380V-60HZ/
460V/575V PWR, EM CNTL

IMPORTANT

DO NOT ENERGIZE UNIT UNTIL
CHECK-OUT AND START-UP
PROCEDURE HAS BEEN COMPLETED.

CAUTION

USE COPPER CONDUCTORS ONLY!

UNIT TERMINALS ARE NOT DESIGNED TO
ACCEPT OTHER TYPES OF CONDUCTORS.

FAILURE TO DO SO MAY CAUSE DAMAGE TO THE EQUIPMENT.

ATTENTION

N'UTILISER QUE DES CONDUCTEURS EN CUIVRE!

LES BORNES DE L'UNITÉ NE SONT PAS CONÇUES POUR RECEVOIR D'AUTRES TYPES DE CONDUCTEURS.

L'UTILISATION DE TOUT AUTRE CONDUCTEUR
PEUT ENDOMMAGER L'ÉQUIPEMENT.

PRECAUCIÓN

¡UTILICE ÚNICAMENTE CONDUCTORES DE COBRE!

LAS TERMINALES DE LA UNIDAD NO ESTÁN
DISEÑADAS PARA ACEPTAR OTROS TIPOS DE
CONDUCTORES.

SI NO LO HACE, PUEDE OCASIONAR DAÑO AL EQUIPO.